PX0837/2M00 Datasheet



Product Name // Overmould Flex Connector PX0837 Series Pre-Wired Patch Cord IP68 RJ45 to Shielded RJ45 2M Cable

View Product Page



// Product Description:

- O Cat 5e and Cat 6a Options
- O Pre-Wired Patch Cord with overmoulded connector(s)
- Water and dustproof to IP68 when mated with compatible connector
- O Supplied with shielded RJ45 plug
- S-FTP cable construction
- PUR jacket cable in a choice of lengths depending on part code suffix
- Choice of:
- O IP68 RJ45 to bare end (part codes prefixed PX0836, PX0896)
- IP68 RJ45 to Shielded RJ45 (part codes prefixed PX0837, PX0897)
- O IP68 RJ45 to IP68 RJ45 (part codes prefixed PX0838, PX0898)
- PX0835 Sealing Cap available separately to maintain IP rating of unmated connectors
- Mate with all PX08 Standard Series RJ45 Panel Mount Connectors

// General Information:

Product Configurator:
Product Display Title:
Product Family:

Product Series: Pdfbuilder Enabled: Change Notes:

Weight:

Product Technical Image: Technical Image:

Body Material: Cable Length: Contact Type: Coupling Type: Current Max: Data Cable Type:

Diameter Over Coupling Ring Mm:

Flamability Rating:

Function: Ip Rating:

Max Operating Temperature:
Min Operating Temperature:
Number Of Contacts:
Rohs Compliant:
Voltage Max:
Package Id:

No

Cat 5e and Cat 6a Options Circular Data Connectors Standard Buccaneer - Ethernet

Yes

PRODUCT-MOQ-ADJUSTMENT

0.217

px0836_2_diagram.jpg px0836_2_diagram.jpg

2m Plug Contact Screw 1.5A

IP68 RJ45 to Shielded RJ45

38.1mm UL94V-0

Flex to Standard Connector Double Ended Cable

IP68, IP69K +70°C -20°C 8 Contacts Yes 42V

564

// Product PDF Links



// Product 3D CAD Model Links



PX0837/2M003D CAD Model