




Geberit Mapress Stainless Steel flange PN 10/16, with pressing socket (FKM, blue)



Example image



APPLICATION PURPOSES

- For chemicals and technical liquids
- For district heating water $\leq 140\text{ }^{\circ}\text{C}$
- For thermal media (solar)
- For mineral and lubricating oil
- For motor fuels (e.g. diesel)
- For compressed air (oil purity class 0–4)
- For solar technology, industry and shipbuilding
- For industrial gases (e.g. acetylene, shielding gases)

CHARACTERISTICS

- Pressing indicator
- Silicone-free (LABS-free)
- Seal ring made of FKM, blue
- Pressing socket with black protection plug
- Design B1 (raised sealing strip with standard sealing strip), EN 1092-1

TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

ACCESSORIES

- Geberit bolt set for flange connection, made of CrNi steel
- Geberit flange gasket, fibre composite material PN 10/16

Art. no.	DN	d, ø mm	di, ø mm	D cm	k mm	m mm	L cm	l cm	Z cm	n pc.	PN bar
50673	15	18	15	9.5	65	14	6.2	1.6	4.2	4	10 / 16
50674	20	22	19	10.5	75	14	6.5	1.8	4.4	4	10 / 16
50675	25	28	25	11.5	85	14	6.9	1.8	4.6	4	10 / 16
50676	32	35	32	14	100	18	7.2	1.8	4.6	4	10 / 16

<i>Art. no.</i>	<i>DN</i>	<i>d, ø</i> mm	<i>d_i, ø</i> mm	<i>D</i> cm	<i>k</i> mm	<i>m</i> mm	<i>L</i> cm	<i>l</i> cm	<i>z</i> cm	<i>n</i> pc.	<i>PN</i> bar
50677	40	42	39	15	110	18	7.9	1.8	4.9	4	10 / 16
50678	50	54	51	16.5	125	18	8.7	1.8	5.2	4	10 / 16
50679	65	76.1	72	18.5	145	18	11.8	1.8	6.5	4	10 / 16
50680	80	88.9	84.8	20	160	18	12.5	2	6.5	8	10 / 16
50681	100	108	103.9	22	180	18	13	2	5.5	8	10 / 16