


Art.-No.	VE	PG	EAN
233202008	1	132	 4 008224 6 188 16

UNOversal Plus, 6-way, with overvoltage filter, optical overvoltage indicator in case of a fault, with illuminated switch (2-pole), with shutter, with 90° turned sockets, 52mm distance between sockets, cable H05VV-F3G1,5mm², 1,4m, mountable, 16A, 250V~, white



Technical data		233202008
Housing shape	Rectangular	
Material	Plastic	
Material quality	Thermoplastic	
Surface protection	Untreated	
Surface finishing	Matt	
Colour	White	
Degree of protection (IP)	IP20	
Angle rotated central insert	90°	
Number of socket outlets with protective contact	6	
Number of Euro socket outlets	0	
Number of CEE socket outlets	0	
Number of socket outlets with earth pin	0	
Number of cold device socket outlets	0	
Residual current circuit breaker (RCCB)	No	
Mains filter	No	
Number of other socket outlets	0	
Over voltage protection	Yes	
Nominal current	16A	
Core cross section	1.5mm ²	
With cover	No	
Transparent	No	
Length of power cord	1.4m	
Rotated central insert	Yes	

