

D-SUB EMC inner sleeve - VS-15-TI-2EMV - 1688065


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



D-SUB EMC inner sleeve, shell size 2, shielded, for sleeve housing VS-15-...



Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 182304
Weight per Piece (excluding packing)	24.23 g
Custom tariff number	85389099
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

General

Type	D-SUB 15
Number of positions	15
Color	Bare metallic
Cable exit	Angled
Housing material	Nickel silver

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701

D-SUB EMC inner sleeve - VS-15-TI-2EMV - 1688065

Classifications

eCl@ss

eCl@ss 5.1	27260701
eCl@ss 6.0	27261203
eCl@ss 7.0	27440290

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC002641
ETIM 5.0	EC002641

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Drawings

Dimensioned
drawing

D-
SUB
EMC
inner
sleeve