

Features

- UL approved Nylon 66, 94V-2
- Color: Black, other special color available.
- Easy to use, double locking mechanism.
- The non-releasable double locking mechanism.
- Easy to thread.

RS PRO Double Locking Cable Ties

RS Stock No.: 6664691



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Introducing the range of RS PRO PA66 (Nylon) Cable Ties, ideal for use when fastening electrical cables or wires. The double locking mechanism ensures a secure hold when tying or fastening items together, while the ultra-durable nylon material provides a strong and long-lasting solution that can withstand harsh environments. In addition to this, the serrations on the cable tie surface provide a strong hold on bundles, even at high tension. These RS PRO cable ties are ideal for use when installing cabling in factories, industrial and manufacturing plants, as well as a wide range of other applications.

General Specifications

Type	Double Locking Cable Tie
Colour	Black
Material	Nylon 66
UV Resistant	No
Fire Behaviour	Self-Extinguishing
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	85°C
Quantity	200

Mechanical Specifications

Length	760mm / 30"
Width	9.0mm / 0.35"
Min. Loop Tensile Strength(lbs/kgf/N)	120lbs / 55kgf / 534N
Maximum Bundle Dia.	230mm

Approvals

Standards Met	RoHS, SVHC, ABS, HF
---------------	---------------------

