# PressurePro Foam Cleaner RM 838 direct

Enables contact-free vehicle washing. Effortlessly removes even stubborn oil and grease deposits, insect residue and road dirt while being gentle on the paintwork.

**pH value 12**
in concentrate




Made in Germany

NTA-free

## Properties

- Powerful foam cleaner for contactless vehicle washing
- removes stubborn oil and grease stains, as well as soot, resin, insect residue and road dirt
- enhanced cleaning performance thanks to microcrystals
- Especially effective due to the fine, voluminous and long-lasting foam
- Brushless cleaning prevents the formation of micro-scratches
- Very gentle on paintwork, decorative trims and aluminium rims
- highly efficient
- Very short contact time
- Pleasant, fresh scent
- VDA-compliant

## Application areas

| | |
|---|---|
| **Car dealership and garage** | Vehicle cleaning |
| **Haulage contractors, bus operators** | Commercial vehicle cleaning |
| **Industry** | Commercial vehicle cleaning |
| **Building Industry** | Commercial vehicle cleaning |
| **Agriculture** | Vehicle cleaning |

## Usage options

- High-pressure cleaner with foam nozzle

## Technical data

| Container sizes | Packaging unit | Part number |
|---|---|---|
| 1 l | 12 Piece(s) | 6.296-034.0 |
| 3 l | 1 Piece(s) | 6.295-979.0 |

We would be happy to advise you:

PressurePro Foam Cleaner RM 838 direct, 0.011-000.0, 2026-05-08

## Application

**High-pressure cleaner with foam nozzle**

- Set the dosage and temperature on the device
- 1-40°C processing temperature.
- Apply foam from bottom to top in even strips.
- Allow to soak.
- Reaction time 1 min.
- Rinse surface well with clear water.



## Instructions for use

- Do not let the cleaning solution dry out.
- Test on an inconspicuous part for material compatibility.
- Do not apply to unpainted or damaged light metal surfaces.
- Store away from frost.

## Warnings and safety recommendations according to EC Directives

- Danger
- H314 Causes severe skin burns and eye damage
- H290 May be corrosive to metals
- H412 Harmful to aquatic life with long lasting effects
- P280 Wear protective gloves/protective clothing/eye protection/face protection.
- P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- P310 Immediately call a POISON CENTER/doctor.
- P303 + P361 + P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water [or shower].
- P405 Store locked up.
- P501a Dispose of contents/container in accordance with local/regional/national/international regulations.
- Z 20 Contains Limonene. May produce an allergic reaction.

## Further information

- VDA certification
- Material Safety Data Sheet (MSDS)

## Dosage and yield

| Contents | Cleaning method | Dosage | Soiling | Yield |
|---|---|---|---|---|
| 1000 ml | High-pressure cleaner with foam nozzle | 1 – 3 % | medium-strong | 20 Car |



We would be happy to advise you: