

Features

- Medium Duty
- Stainless Steel
- Industrial castor
- Rotation Swivel
- Fixing Hole
- Polyamide 6
- Corrosion Resistant
- Impact Resistant
- Shock Absorbing

RS PRO Castor Wheels

RS Stock No.: 0149254



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description







Polyamide 6 wheel. Hub on plain bore. In pressed stainless steel AISI 304, turning on double rim of balls in stainless steel AISI 420. Assembled with self-locking nut.

General Specifications

Rotation	Swivel
Weight Class	Medium Duty
Load Capacity (Kg)	170
Load Capacity / 4pcs (Kg)	680
Tyre Material	Polyamide 6
Hub Material	Polyamide 6
Bracket Material	Pressed Stainless Steel
Includes Brake	No
Features	Corrosion Resistant, Impact Resistant, Shock Absorbing
Applications	Industrial castor

Operation Environment Specifications

Operating Temperature (Celsius)	-25° to 85°
---------------------------------	-------------

					
125x40	42	150	12	170	220

Mechanical Specifications

Mounting Type	Single Bolt
Wheel Diameter (mm)	125
Wheel / Tread Width (mm)	40
Overall Height (mm)	150
Number of Fixing Holes	1
Fixing Hole Size (mm)	12
Hub Bearing Type	Plain Bore
Thread Size (M)	
Stem Height (mm)	
Stem Diameter (mm)	
Hardness of Wheel (Shore A)	
Levelling Extent (mm)	
Offset (mm)	42
Castor Weight (Kg)	0.739

Fixing Centres Specifications

Fixing Centres (mm)	
Fixing Centres Length (mm)	
Fixing Centres Width (mm)	

Fixing Plate Specifications

Fixing Plate Dimensions (mm)	
Fixing Plate Length (mm)	
Fixing Plate Width (mm)	