

Datasheet

RS Pro Emergency Light Fitting 2 x 21 W Halogen 315 x 310 x 110 mm

RS Stock No: **494-7880**



Product Details

RS Pro halogen emergency light fitting is a non-maintained luminaire, illuminates only on a failure of the mains supply. It has 2 x 21 W power rating. It has a optional switch for testing emergency mode and LED indicator to show battery charge status. It is suitable for emergency exits, switchrooms and storage areas.

Features and Benefits

- Optional - switch for testing emergency mode
- Powered by 2 x 6 V 12 Ah batteries
- Battery cut-off prevents deep discharge
- LED indication of battery charge status
- Ideal for emergency exits, switchrooms and storage areas

Specifications:

Anti-corrosive	No
Depth	110 mm
Dimensions	315 x 310 x 110 mm
Duration	3 h
EU Energy Efficiency Rating	B
Fitting Type	Twin Spot
Lamp Supplied	Yes
Lamp Type	Halogen
Length	315 mm
Luminosity	280 lm
Maintained	Non Maintained
Standards Met	CE Certified
Wattage	2 x 21 W
Width	310 mm
Case Material	PC