

Extra Hard for internal Torx® screws



PRODUCT PROPERTIES		ORDERING INFORMATION				
Dimensions	Length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number
Drive ISO 1173 C6.3, 1/4" external hex shank						
T30	25	P1k	25	25	3165140798181	2 608 522 272
Drive ISO 1173 E6.3, 1/4" external hex shank						
T8	49	PC1d	1	5	3165140301541	2 607 001 628
T9	49	PC1d	1	5	3165140301565	2 607 001 630
T10	49	PC1d	1	5	3165140301596	2 607 001 632
T15	49	PC1d	1	5	3165140301602	2 607 001 634
T20	49	PC1d	1	5	3165140301626	2 607 001 636
T25	49	PC1d	1	5	3165140301640	2 607 001 638
T27	49	PC1d	1	5	3165140301664	2 607 001 640
T30	49	PC1d	1	5	3165140301688	2 607 001 642
T40	49	PC1d	1	5	3165140301701	2 607 001 644
T25	49	P1b	25	1	3165140354394	2 607 002 512
T30	49	P1b	25	1	3165140354417	2 607 002 514
Drive ISO 1173 E6.3, 1/4" external hex shank						
T8	89	PC1d	1	5	3165140301725	2 607 001 646
T10	89	PC1d	1	5	3165140301749	2 607 001 648
T15	89	PC1d	1	5	3165140301763	2 607 001 650
T20	89	PC1d	1	5	3165140301787	2 607 001 652
T25	89	PC1d	1	5	3165140301800	2 607 001 654
T27	89	PC1d	1	5	3165140301824	2 607 001 656
T30	89	PC1d	1	5	3165140301848	2 607 001 658
T40	89	PC1d	1	5	3165140301862	2 607 001 660
Drive ISO 1173 E6.3, 1/4" external hex shank						
T8	152	PC1d	1	5	3165140301886	2 607 001 662
T10	152	PC1d	1	5	3165140301909	2 607 001 664
T15	152	PC1d	1	5	3165140301923	2 607 001 666
T20	152	PC1d	1	5	3165140301947	2 607 001 668
T25	152	PC1d	1	5	3165140301961	2 607 001 670
T27	152	PC1d	1	5	3165140301985	2 607 001 672
T30	152	PC1d	1	5	3165140302005	2 607 001 674