

Han B Protect Cover Die Cast f Hood PG16



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 010 5457
Specification	Han B Protect Cover Die Cast f Hood PG16
HARTING eCatalogue	https://harting.com/09300105457

Identification

Category	Accessories
Series of hoods/housings	Han [®] B
Type of accessory	Protection cover
Description of the accessory	for hoods With fixing cord

Version

Size	10 B
Locking type	Double locking lever (on the hood)

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Metal
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	55.805 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140045385
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467