

53543

Tube Brush f/flexible handle
53515 or 53525, 200 mm,
Medium, Blue



Brush for flexible handle, 53515 and 53525 Suitable for cleaning pipes in dairies, breweries and the fishing industry.

Technical Data

Item Number	53543
Visible bristle length	5 mm
Material	Polypropylene Polyester Stainless Steel
Suitable for Food Contact (EU 1935/2004), DoC ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	5060 Pcs
Quantity Per Layer (Pallet)	0 Pcs.
Box Length	280 mm
Box Width	125 mm
Box Height	80 mm
Product Diameter	12 mm
Length	200 mm
Width	12 mm
Height	12 mm
Gross Weight	0,031 kg
Net Weight	0,023 kg
Cubik metre	0 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Gtin-13 Number	5705020535437
GTIN-14 Number (Box quantity)	15705020535434
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its

intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact