

PRODUCT DATASHEET

DULUX D/E LED HF 10 W/3000K

OSRAM DULUX D/E LED HF | LED replacement for CFLni, 2 tubes, with 4-pin G24q base for ECG and AC mains operation



AREAS OF APPLICATION

- Supermarkets and department stores
- Walkways and corridors
- Hotels, restaurants
- Outdoor applications only in suitable luminaires

PRODUCT BENEFITS

- LED replacement for conventional compact fluorescent lamps for use in ECG luminaires or on AC mains
- Quick, simple and safe replacement
- Rotatable base around its longitudinal axis ($\pm 90^\circ$)
- Low energy consumption

PRODUCT FEATURES

- Single-ended four-pin plug-in G24q base
- Type of protection: IP20
- Lifetime: up to 30,000 h
- Mercury-free lamps



TECHNICAL DATA

Electrical data

Rated wattage	10.00 W
Nominal wattage	10.00 W
Nominal voltage	220...240 V
Max. lamp no. on circuit break. 10 A (B)	95
Max. lamp no. on circuit break. 16 A (B)	150
Operating frequency	50...60 Hz
Inrush current	20.0 A
Power factor λ	> 0.90

Photometrical data

Nominal luminous flux	920 lm
Rated luminous flux	920 lm
Rated color temperature	3000 K
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Warm White
Color temperature	3000 K
Luminous flux	920 lm
Color rendering index Ra	≥ 80
Standard deviation of color matching	≤ 6 sdcn
Color rendering index Ra	≥ 80

Light technical data

Warm-up time (60 %)	< 0.50 s
Beam angle	120 °
Starting time	< 0.5 s

Dimensions & weight



Overall length	171.0 mm
Diameter	35.0 mm
Outer bulb	-
Length	171.0 mm

Temperatures & operating conditions

Maximum temperature at tc test point	73 °C
---------------------------------------------	-------

Lifespan

Nominal lamp life time	30000 h
Rated lamp life time	30000 h
Number of switching cycles	200000
Lumen maintenance at end of service life	0.70

Additional product data

Base (standard designation)	G24q-3
Mercury content	0.0 mg
Mercury-free	Yes
Design / version	Frosted
Show WEEE picto	Yes

Capabilities

Dimmable	No
-----------------	----

Certificates & standards

Energy efficiency class	A+
Energy consumption	10 kWh/1000h

Country-specific categorizations

Order reference	DULUXDE26LED10W
------------------------	-----------------

SAFETY ADVICE

Only suitable for temperatures of up to 35°C inside of the luminaire.
 Always check the latest update of the compatibility list available on www.ledvance.com/ecg-compatibility
 Not suitable for operation with conventional control gear
 Not suitable for tandem operation.

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
--------------	------------------------------	--------------------------------------	--------------	--------

4058075135246	Folding carton box 1	37 mm x 37 mm x 174 mm	103.40 g	0.24 dm ³
4058075135253	Shipping carton box 10	205 mm x 91 mm x 200 mm	1177.00 g	3.73 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.