



Technical Specification

CCPBR0625AB - 6A 6KA Class A Type B SP Compact RCBO



General

Trade price: £19.86

Box quantity: 5

Total gross weight (g) includes packing: 759.00

Total net weight (g) excluding packaging: 689.00

Individual unit weight (g): 138.00

Width mm: 19.00

Height mm: 90.00

Depth mm: 75.00

Size/Dimensions (mm): 19X90X75

Surf area M²: 0.020

Technical

ABC indicator: A

Colour: White

Associated standards: BS EN 61009

Rated voltage: 220-250V

Rated kA: 6

Rated current: 25A

Frequency: 50-60Hz

Wiring system: 1 pole

Ambient operating temperature:

-5 to 40°C (24hour average not exceeding 25°C)

Width in number of modular spacings: 1

Nature of supply: AC

Rated fault current: 30mA

Release characteristic: B

Mounting method: DIN Rail