

Previously known as: MICROCHEM® 4000 Overboots - Model 406

Engineered to provide an exceptional barrier against a wide range of organic and inorganic chemicals and biological agents..

DESIGN

A unique multi-layer barrier fabric renowned for its lightweight, yet robust textile feel and exceptional barrier to organic & inorganic chemicals.

ULTRASONICALLY WELDED SEAMS

Provides a strong liquid and particle barrier, made from the same fabric as the suit to maintain the same chemical resistance



Industries

- Chemical
- Life Sciences
- Mining
- Fire and Rescue
- Oil and gas
- Automotive Aftermarket
- Food Processing

Applications

- Contaminated Environments
- Chemical Handling
- Filling, blending and charging of raw materials
- Transferring liquids and solids
- Opening and draining pumps valves or lines
- Loading and unloading of process equipment
- Raw material sample collection
- Concentration mixing and palletisation
- Hazmat response
- Assembly and disassembly of equipment


KEY FEATURES & BENEFITS

- Exceptional protection, over 200 chemicals permeation tested, including chemical warfare agents
- Designed to protect
- Silicone free


Technology



Material Diagram



Seam Diagram



Performance Standards


0598

EN ISO 13688:2013


EN 14126


PARTIAL BODY
PROTECTION ONLY


TYPE PB [3]


TYPE PB [4]

Product Information

Product Information	
Available Sizes	One Size
Color	Green
Country Of Origin	China
Packaging Overview	20 PR in a compressed bag
Product Material	Multi-layer non-woven barrier Laminate fabric
Product Reference	4000 Overboots - Model 406
Seam Type	Welded
Shelf Life	5 years

Suit components & accessories

Suit Components and Accessories	
Design Features	Overboots, elastic to top of boot, tie fastening and welded seams.

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

