

HT-680R | DUAL LED HIGH CRI HEADTORCH

- 680 lumen white spot beam Cree LED, 6500k
- Secondary 500 Lumen warm white flood beam high CRI 90+ Cree LED, 4500k
- Memory Switch remembers last mode used
- Super tough construction with rubberised coating Im USB-C charging cable included
- Fully adjustable non-slip silicone lined headband
- 4 x Helmet clips included
- 90° rotational head
- IP65 dust & water resistant

- IK07 shock proof 2m drop resistant
- Rechargeable 3.7v 2600mAh Li-ion battery
- Useful battery level and charging indicator
- Quick 4.5 hour USB-C charge time

BATTERY 3.7v 2600mAh Li-Ion Battery WEIGHT 175g **DIMENSIONS** headtorch W56 x H35 x D25mm / battery pack: W86 x H36 x D37 mm

LUMEN 680LM | RUNTIME 4-30H | BEAM 89M | IP RATING IP65/IK07

#BUILT TOUGH