

# CIRCLIP PLIER INNER STRAIGHT PRO 175MM



- Invisible return spring for easier operation
- For use with inner type circlips or snap rings
- Bearing steel tips for heavy duty applications
- Non slip tip angle enabling the ring to stock securely to the tip when compressing or expanding the circlip
- Chrome vanadium construction
- Vinyl grip for easier use in pockets or tool pouches
- DIN 5256

7" Straight/Inner Circlip Plier Vinyl Grip with Spring

## General information

**Country of origin:** Taiwan  
**Barcode:** 5020385071810  
**Tariff code Europe:** 8203200000  
**ECCN US:** EAR99  
**ETIM:** EC002228  
**UNSPSC:** 27112110

## Dimensions

**Net weight (g):** 158  
**Length:** 185 mm  
**Length 2:** 7"

## Attributes

**Product type:** Circlip Pliers  
**Material:** CrV, Bearing Steel  
**Certificates:** N/A  
**Size:** 1.8 mm  
**Capacity (mm):** 19-60  
**Handle type:** Vinyl  
**Return spring:** Yes  
**Tip or blade type:** Straight, Inner

## Features



 **DESIGNED IN SWEDEN**

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.

Technical changes and errors may occur. 01-08-2024 19:50



Sandbergsvägen 3  
441 39 Alingsås, Sweden