



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Telephone cable User manual USB cable
--------------------	---

Physical

Cable length	1.52 m
Depth	38 cm
Height	30.1 cm
Net weight	11.6 kg
Width	11.2 cm

Input

Network frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	French/Belgian
Input voltage limits	156...300 V adjustable 176...294 V
Input voltage	230 V

Output

Rated power in W	720 W
Maximum configurable power in W	720 W
Output frequency	50/60 Hz +/- 3 Hz sync to mains
UPS type	Line interactive
Wave type	Stepped approximation to a sinewave

Nb of power socket outlets	3 French/Belgian 3 French/Belgian surge
Output voltage	230 V

Conformance

Product certifications	CE
Equipment protection policy	Lifetime : 150000 euros

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...30000 ft
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Acoustic level	45 dBA

Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	8 h
Number of battery replacement quantity	1
Liquid value	0

Communications & Management

Control panel	Multifunction LCD status and control console
---------------	--

Surge Protection and Filtering

Surge energy rate	441 J
Data line protection	RJ11 analog phone line for phone/fax/modem/DSL RJ45 network line - 10/100/1000 Base-T Ethernet

Packing Units

Package 1 Weight	13.2 kg
Package 1 Height	38.7 cm
Package 1 width	23.8 cm
Package 1 Length	48.8 cm
SCC14	10731304268724
Number of Units in Package 2	1
Package 2 Weight	27.67 kg
Number of Units in Package 3	16

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Optimized Energy Efficiency	Energy efficient product
-----------------------------	--------------------------

Contractual warranty

Warranty	2 years repair or replace, 3 years repair or replace for European Union countries
----------	---
