



Part Number : [191640065](#)
Product Description : Perma-Seal Ring Tongue
Terminal for 12-10 AWG Wire, Stud Size 10 (M5),
Carton
Series Number : 19164
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : SC-230-10



Documents & Resources

Drawings

[191640065 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19164
Description	Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	Perma-Seal
Type	Ring
UPC	800753113497

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	NiAc
Material - Plating Mating	Tin
Net Weight	2.670/g
Packaging Type	Carton
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm

Stud Size	10 (M5)
Wire Insulation Diameter	7.87mm
Wire Size (AWG)	10, 12
Wire Size mm ²	3.09-5.01

Application Tooling

Global

Description	Part Number
Power Crimp Tool Head for Terminals 22-10 AWG Wire	<u>640057400</u>
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	<u>640160041</u>