



PROFESSIONAL GRADE. PREMIUM EXPERIENCE.

THE S3700

MULTICOLOUR +
SHAPE CUTTER

Enhanced capabilities for a flawless facility



Faster speeds. More options. Smoother operations.

Let your labelling take shape with the S3700.

Elevate your labelling with these advanced features:

- ▶ Seamless multicolour for more impactful labels, signs and tags
- ▶ Precision XY cutter for smooth curved label cutt-outs
- ▶ Auto adjustments that help ribbon cartridges last up to 60% longer
- ▶ 20-second material changeovers and up to 127mm-per-second print speed
- ▶ Onboard label templates and over 600 built-in symbols
- ▶ Broad path prints and outputs labels up to 101.6mm

ANY USER — VIRTUALLY ANY LABEL, SIGN OR TAG



AUTO SETUP
No calibrating, no
threading, no expertise
needed



TAP, PRINT, GO
Onboard templates for
streamlined productivity



EASY CONNECT
PC software and a mobile
app add flexibility

THE S3700 POWERFUL, PRECISE PRODUCTION

Get the job done right for any application

Optimise your performance with the S3700 and Brady materials



SAFETY & FACILITY

- ▶ ISO-7010 Warning, Prohibition, Mandatory, Fire and Evacuation, GHS, CLP, ADR, pipe marking and hazard instructions
- ▶ Multicolour optimised for more impact and less hassle
- ▶ Material durability up to 10 years outdoor in the most harsh environments



LEAN MANUFACTURING

- ▶ Gauges, equipment, calibration, 5S, racks, floor marking and parts bins
- ▶ Built-in XY plotter cutter to slice any shape and letter flawlessly
- ▶ Mobile app so you can take stock of your facility while the printer stays put



OPERATIONS


- ▶ Work in process, quality control, barcodes, area marking and serial numbers
- ▶ Create and print the most commonly used barcode types
- ▶ 600+ pre-programmed symbols



Enjoy a more premium labelling experience with optimised Brady Authentic materials

Authentic materials work seamlessly with Brady printers to produce enhanced performance and reliability you just don't get with materials from the others. We've got you covered with the widest range of colours, finishes and targeted applications in the industry. Get authentic. Get better with Brady.

100s of purpose-built materials for the applications you need

A few S3700 label materials you need to know about		     					
To view all available material options, visit bradyeurope.com/S3700materials		Indoor/ Outdoor	Frozen Surface	General	Safety	Lean/5S	Harsh Environment
B-595 All-Weather Permanent Adhesive Vinyl Tape							
B-581 Repositionable Multi-Purpose Vinyl Tape							
 B-509 Magnetic Labels							
 B-854 ToughWash Washdown Resistant							
B-569 Low-Halide Polyester							
B-851 Tags							
 B-549 Cold-Temperature Application							
B-526 High Intensity Photoluminescent							

 = Unique Brady material

▶ Learn more at bradyeurope.com/S3700 or scan to watch the overview video



S3700 Printer Specifications

Specifications	
Print Technology	Thermal Transfer
Print Resolution (dpi)	300 dpi
Print Speed (mm/sec)	127.00 mm/s
Colour Capability	Multicolour, Monocolour
Continuous vs Die-cut Labels	Continuous and Die-cut
Max. Label Width (mm)	101.60 mm
Max. Print Length	2530 mm
Connectivity Options	Bluetooth Wi-Fi Ethernet USB
Software Compatibility	Brady Workstation Express Labels Mobile App Windows based driver for 3rd party software use
Bar Code Type	Code 128 Auto Code 39 Interleaved 2 of 5 More through Brady WorkStation EAN-13 UPC-A
Built-in Symbols	664
Physical Properties	
Width x Height x Depth (mm)	482.60 x 279.40 x 361.95
Weight (kg)	16.74 kg
On Screen Indicators	Data Reception Error Messaging Ribbon and label part number recognition Supply Remaining WiFi Ethernet Status Bluetooth Status
Cutter	XY Cutter and Auto Cutter
Warranty	1 year



S3700 Label Printers

Article No.	Description
176427	S3700 Multicolour & Cut Sign and Label Printer with QWERTZ keyboard, Wifi and Bluetooth enabled
176428	S3700 Multicolour & Cut Sign and Label Printer with QWERTZ keyboard
176429	S3700 Multicolour & Cut Sign and Label Printer with AZERTY keyboard, Wifi and Bluetooth enabled
176430	S3700 Multicolour & Cut Sign and Label Printer with AZERTY Keyboard
176431	S3700 Multicolour & Cut Sign and Label Printer with QWERTY EU keyboard, Wifi and Bluetooth enabled
176432	S3700 Multicolour & Cut Sign and Label Printer with QWERTY EU keyboard
176433	S3700 Multicolour & Cut Sign and Label Printer with QWERTY UK keyboard, Wifi and Bluetooth enabled
176434	S3700 Multicolour & Cut Sign and Label Printer with QWERTY UK keyboard
176435	S3700 Multicolour & Cut Sign and Label Printer with CYRILLIC keyboard, Wifi and Bluetooth enabled
176436	S3700 Multicolour & Cut Sign and Label Printer with CYRILLIC keyboard

Accessories

Article No.	Description
036612	Squeegee
133251	Printer Cleaning Kit, Thermal Transfer Printers
142114	Media Wiper 5 Pack
142116	Cutter Cleaning Tool for BBP30, BBP31, BBP33, S3100, S3700 and i3300 printer



S3700 Label Printer Kit

Article No.	Description
321264	S3700 Multicolour & Cut Sign and Label Printer with QWERTZ keyboard, Wi-Fi and Bluetooth + BWS Suite
321265	S3700 Multicolour & Cut Sign and Label Printer with QWERTZ keyboard + BWS Suite
321266	S3700 Multicolour & Cut Sign and Label Printer with AZERTY keyboard, Wi-Fi and Bluetooth + BWS Suite
321267	S3700 Multicolour & Cut Sign and Label Printer - AZERTY Keyboard + BWS Suite
321268	S3700 Multicolour & Cut Sign and Label Printer with QWERTY EU keyboard, Wi-Fi and Bluetooth + BWS Suite
321269	S3700 Multicolour & Cut Sign and Label Printer - QWERTY EU keyboard + BWS Suite
321270	S3700 Multicolour & Cut Sign and Label Printer with QWERTY UK keyboard, Wi-Fi and Bluetooth + BWS Suite
321271	S3700 Multicolour & Cut Sign and Label Printer - QWERTY UK keyboard + BWS Suite
321272	S3700 Multicolour & Cut Sign and Label Printer with CYRILLIC keyboard, Wi-Fi and Bluetooth + BWS Suite
321273	S3700 Multicolour & Cut Sign and Label Printer - CYRILLIC keyboard + BWS Suite

