

HOSE COILS

DIFLEX PVC hose - Coil



Part number	Length (m)	Radius of curve (mm)	Max. operating pressure (bar)	Net weight (Kg)	Color
DIFLEX 6	50.00	36.00	15.00	0,097	Blue
DIFLEX 8	50.00	54.00	15.00	0,123	Blue
DIFLEX 8C25	25.00	54.00	15.00	0,123	Blue
DIFLEX 10	50.00	74.00	15.00	0,144	Blue
DIFLEX 10C25	25.00	74.00	15.00	0,144	Blue
DIFLEX 12	50.00	90.00	15.00	0,201	Blue
DIFLEX 13	50.00	101.00	15.00	0,214	Blue
DIFLEX 19	25.00	174.00	15.00	0,304	Blue
DIFLEX 25	25.00	260.00	15.00	0,448	Blue

Part number	Ø int/ext (mm)
DIFLEX 6	6.00 / 12.00
DIFLEX 8	8.00 / 14.00
DIFLEX 8C25	8.00 / 14.00
DIFLEX 10	10.00 / 16.00
DIFLEX 10C25	10.00 / 16.00
DIFLEX 12	12.00 / 19.00
DIFLEX 13	13.00 / 20.00
DIFLEX 19	19.00 / 26.00
DIFLEX 25	25.00 / 33.00