



## Notice : 1547 150 PA

Index : 3

### GUYARD SAS

22-24, rue Lucien Rouzet  
Z.A. Villedieu sur Indre/Niherne  
36250 NIHERNE FRANCE

### Intermediate risks - Category II PPE

EN 21420 :2020 EN 388 :2016+A1 :2018  
EN 407 : 2020 EN ISO 13997 :1999  
EN 12477 :2001 +A1 :2005 Type A

### FEATURES :

- 5 -finger glove in flame-retardant cowhide.
- 150mm natural crust cuff.
- Protection of the artery.
- Heat-resistant.
- Aramid thread stitching.

### AVAILABLE SIZE :

- Sizes 8 to 11

### PRECAUTIONS FOR USE :

- Wear gloves on clean, dry hands. Pre-testing of gloves is recommended. Actual conditions of use may differ from EU type testing.
- Before re-use, check gloves for defects, holes, tears or abnormal wear.
- Shelf life: 5 years from the date of manufacture indicated on the glove.

### SAFETY COMFORT AND DEXTERITY :

- Dexterity level 5
- The glove does not contain substances at levels known or suspected to have adverse effects on the hygiene or health of the user under the foreseeable conditions of use.

### PACKAGING

- In the event of deconditioning, a copy of the package leaflet must be enclosed with the smallest package.
- Pack of 10 pairs
- Box of 100 pairs.

### MARKING :

- The CE mark affixed to this glove signifies compliance with the essential health and safety requirements of European Regulation 2016/425 on personal protective equipment (PPE).

### RECOMMENDED USES :

- Gloves designed for welding work.

EN 21420 :2020 EN 388 :2016A1 :2018

EN 407 :2020



3 1 4 4 A



4 1 3 2 4 X

### PERFORMANCE LEVELS :

#### EN 388 :2016+A1 /2018

- |   |     |
|---|-----|
| • Abrasion :                            | 3/4 |
| • Blade cut :                           | 1/5 |
| • Tear :                                | 4/4 |
| • Puncture :                            | 4/4 |
| • Cutting by sharp objects (ISO 13997): | A/F |

#### EN 407 :2020

- |                                    |     |
|------------------------------------|-----|
| • Fire behavior :                  | 4/4 |
| • Heat contact :                   | 1/4 |
| • Convective heat :                | 3/4 |
| • Radiant heat :                   | 2/4 |
| • Small splashes of liquid metal : | 4/4 |
| • Large splashes of liquid metal : | X   |

#### EN 12477 :2001+ A1 /2005

- |          |   |
|----------|---|
| • Type : | A |
|----------|---|

### PROTECTION LIMITS

- Do not use for handling objects at temperatures over 100°C.
- Not suitable for handling chemicals.

### MAINTENANCE AND STORAGE

- No special maintenance is recommended. Products should be stored in a cool, dry, well-ventilated place away from direct light.

### END OF LIFE

- End-of-life destruction must be controlled and comply with European traceability and environmental requirements.

EU Type Certificate issued in accordance with Module B Regulation (EU) 2016/425  
The EU Declaration of Conformity is available on

LEITAT ON n° : 0162  
www.guyard-sa.com