

## Features

- **Precise Fit for DIAZED Fuses** – Specifically designed for E27 or E33 (DII + DIII) fuses to ensure accurate and secure installation.
- **Durable & Non-Conductive Material** – Made from tough, chemical-resistant, and electrically insulated plastic for safe use in harsh environments.
- **High Visibility Compliance Label** – Prominent “Danger – Do Not Operate” warning enhances visibility and safety awareness.
- **Padlock-Compatible Design** – Includes a top hole that supports padlocks with up to 6.5mm shackle diameter for secure lockout.
- **Special Black Key Included** – Comes with a custom key for quick and efficient lockout and removal operations.
- **Key Loss Prevention Tip** – Users are advised to store the key with the padlock shackle to prevent misplacement.

## RS PRO Lockout Insulation Plugs for Bottle Fuses for E27 or E33 (DIAZED DII+DIII)

RS Stock No.: 0710489



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

- *Specially engineered for E27/E33 (DII/DIII) bottle fuses to prevent accidental energization during maintenance.*
- *Made of rugged, non-conductive material that resists chemicals and withstands industrial environments.*
- *Bright warning label ensures clear communication of lockout status to all personnel.*
- *Easy to apply using a padlock (up to 6.5mm shackle), ensuring a tamper-resistant setup.*
- *Supplied with a unique black key to simplify secure application and removal.*
- *Best practice: keep the key attached to the padlock to avoid misplacement during procedures.*

## General Specifications

|               |                     |
|---------------|---------------------|
| Type          | Fuse Lockout        |
| Material      | ABS                 |
| Colour        | Red, Yellow & Black |
| Padlock holes | 01                  |
| Package       | PE-LD               |

## Mechanical Specifications

|   |          |
|---|----------|
| Height (with black key)                         | 104mm    |
| Height (without key)                            | 71.30mm  |
| Diameter (Red Cap)                              | 34.72mm  |
| Diameter (Yellow Body)                          | 33.94mm  |
| Attachment Point for Padlock (Shackle Diameter) | 7mm      |
| Weight  | 32 Grams |

## Operation Environment Specifications

|                       |                                   |
|-----------------------|-----------------------------------|
| Withstand temperature | -40°C to +105°C (-40°F to +221°F) |
|-----------------------|-----------------------------------|