

Circular Saw LXT®

DHS900

18V X2 • 4 500 min⁻¹ • 235 mm

Highly robust circular saw for demanding applications

Highly efficient cordless saw for heavy duty use. The brushless 36V motor uses two 18V batteries. The large 235 mm blade rotates at 4 500 rpm. Cutting depth 85 mm. Suitable for direct use with the guide rail.



Technical specifications

Nominal Battery Voltage	2 x 18 V
Voltage LXT	✓
Max. Cutting Depth at 90°	85 mm
Max. Cutting Depth at 45°	61 mm
No load speed	4500 min ⁻¹
Sound Power Level (L _{WA})	104 dB(A)
Sound Pressure Level (L _{pA})	96 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	5,3 - 6,0 kg
Product Dimensions (L x W x H):	413 x 196 x 316 mm
Brushless Motor	✓
Max. Cutting Depth at 60°	44 mm
AWS ready	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion

User benefits

- 36V performance from two 18V batteries connected in series. The batteries are placed in parallel in separate battery docking stations.
- Magnesium components create lightweight saws that are well-balanced and job site tough
- Brushless maintenance-free and long-life motor
- Battery protection system automatically shuts off power when the battery level is low
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth

Link to product - www.makitauk.com



Related products

Optional AC

162687-7

Tool Guide



194367-7

Guide rail, 3 000 mm



198885-7

Guide rail joint connector set, 2 pcs



199140-0

Guide rail, 1 000 mm



199826-6

Quick-Release Ratcheting Guide Rail



783204-6

Hex Wrench 6Mm



E-01915

Circular Saw Blade, Efficut T.C.T, 235



E-05664

Guide Rail Protective Holder



E-05670

Guide Rail Protective Holder



Other

User manual

Parts drawing