

Features

- Engineered for high-performance, fast cutting through metal.
- 1.8mm tooth pitch delivers precise, efficient cuts in pipes and profiles from 2.0-8.0mm.
- The 150mm blade length provides a cutting capacity of up to 100mm.

Reciprocating Saw Blade - Metal 150 x 19 x 0.9mm - Fast Cut

RS Stock No.: 0757824



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Reciprocating Saw Blade

0757824 Metal Reciprocating Saw Blade is engineered for high-performance, fast cutting through metal. Manufactured from premium M2 High Speed Steel for increased durability and an extended working life, it's the ideal solution for cutting regular-strength steel. A 1.8mm tooth pitch delivers precise, efficient cuts in pipes and profiles from 2.0-8.0mm, while the 150mm blade length provides a cutting capacity of up to 100mm.

- *Manufactured with 6150 Chromium-Vanadium Spring Steel & M2 High Speed Steel teeth*
- *Universal Fitting, compatible with all S-shank 1/2" Reciprocating Saws*
- *Suitable for use on Sheet Metal, Pipes, Profiles and Box Section*
- *Supplied in 5pc Packs*

General Specifications

Tooth Design	Side Set, Milled
Type	Reciprocating Saw Blade
Teeth Spacing	1.8mm
TPI	14
Thickness	0.9mm
Max Cut Depth	100mm
Cut Type	Fast Cutting
Blade Material	M2 High Speed Steel
Body Material	6150 Chromium-Vanadium Spring Steel
Fitting	S-Shank 1/2"
Length	150mm
Width	19mm

Stock No.	Cut Type	Thickness	Length	Width
XXX-XXXX 0757823	Progressive Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757824	Fast Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757825	Precision Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757826	Fine Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757827	Fast Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757828	Precision Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757830	Fine Cutting	0.9mm	225mm	19mm

Approvals

Declarations	REACH DoC
---------------------	-----------

Similar Products

Stock No.	Brand	Product Name	Cut Type	Thickness	Length	Width
XXX-XXXX 0757823	RS PRO	Reciprocating Saw Blade	Progressive Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757824	RS PRO	Reciprocating Saw Blade	Fast Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757825	RS PRO	Reciprocating Saw Blade	Precision Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757826	RS PRO	Reciprocating Saw Blade	Fine Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757827	RS PRO	Reciprocating Saw Blade	Fast Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757828	RS PRO	Reciprocating Saw Blade	Precision Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757830	RS PRO	Reciprocating Saw Blade	Fine Cutting	0.9mm	225mm	19mm

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories