

[Home](#) > [Products](#)

X20cMK0213

Technical Data	Basic Information
<p>General information ▼</p>	
<p>Memory size</p>	<p>8 MB</p>
<p>Application memory</p>	
<p>Guaranteed erase/write cycles</p>	<p>100,000</p>
<p>Certifications</p>	
<p>CE</p>	<p>Yes</p>
<p>UL</p>	<p>cULus E115267 Industrial control equipment</p>
<p>DNV</p>	<p>Temperature: B (0 to 55°C) Humidity: B (up to 100%) Vibration: B (4 g) EMC: B (bridge and open deck)</p>
<p>LR</p>	<p>ENV1</p>
<p>KR</p>	<p>Yes</p>

Operating conditions**Mounting orientation**

Horizontal	Yes
Vertical	Yes
Installation elevation above sea level	0 to 2000 m, no limitation
Degree of protection per EN 60529	IP20

Ambient conditions**Temperature**

Operation	
Horizontal mounting orientation	-40 to 60°C
Vertical mounting orientation	-40 to 60°C
Derating	-
Storage	-40 to 85°C
Transport	-40 to 85°C

© 2026 B&R | [Imprint](#) | [Privacy notices](#) | [Accessibility Statement](#) | [GTC](#) | [Cookie Settings](#)