

Han EMC/B 6 Protect Cover metal



Image is for illustration purposes only. Please refer to product description.

Part number	09 62 806 5425
Specification	Han EMC/B 6 Protect Cover metal
HARTING eCatalogue	https://harting.com/09628065425

Identification

Category	Accessories
Series of hoods/housings	Han [®] EMC/B
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings With fixing cord

Version

Size	6 B
Locking type	Single locking lever
Details	Not suitable for housings with external seals.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	44 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140191891
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467