

NSYCVF54M230MM2

Climasys forced vent. 54 m³/h, 230V, 2 metal grilles and 2 anti-insect filters



Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Type of ventilation filter	Anti-insect
Air flow	Overall flow rate : 54 m ³ /h at 50 Hz Free flow rate without filter or grille : 170 m ³ /h
Input voltage	230 V 50/60 Hz

Complementary

Height	External : 120 mm
Width	External : 120 mm
Depth	External : 38 mm
Cut-out dimensions	96 x 96 mm
Material	Steel for outlet grille Stainless steel 304L for filter
Colour	Outlet grille : grey RAL 7035
IP degree of protection	IP33
Device composition	1 axial motor 1 power cord 2 anti-insect filter 2 metal louvre

Environment

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------