

FEATURES

- **UV Resistant:** Ensures longevity and performance in outdoor conditions
- **Tensile Strength of 18 kg:** Provides robust support for bundled cables
- **Operating Temperature Range -40 °C to 85 °C:** Suitable for diverse environmental conditions
- **Maximum Bundle Diameter of 31 mm:** Accommodates a wide range of cable sizes
- **Width of 3.5 mm:** Offers a balance between flexibility and strength
- **UL 94 V-2 Fire Behaviour:** Meets safety standards for flammability

RS PRO Standard Cable Tie, Black Polyamide

RS Stock No: 642-841



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO standard cable ties are designed for securing and organising cables efficiently. Made from durable polyamide, they are ideal for both indoor and outdoor applications, providing reliable performance in various environments.

General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Standard
Tensile Strength	18 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	140 mm
Material	Polyamide
Maximum Bundle Diameter	31 mm
Width	3.5 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
Minimum Operating Temperature	-40 °C

Approvals

Standards/Approvals	ISO 9001 SGS, REACH, RoHS, UL94V-2
---------------------	------------------------------------