



Main

Range	Resi9
Product or component type	Door
Accessory / separate part category	Enclosure accessory
Range compatibility	Resi9 enclosure

Complementary

Type of front cover	Transparent
Number of horizontal rows	4
9 mm pitches	36
Number of 18 mm modules per row	18
Total number of 18 mm modules	72
Standards	IEC 60670-1-24 IEC 61439-3 IEC 61439-1
Fire resistance	750 °C conforming to EN/IEC 60695-2-11
IP degree of protection	IP40 conforming to EN/IEC 60529
IK degree of protection	IK08 conforming to IEC 62262 IK08 conforming to EN 50102
Net weight	1050 g
Width	352.5 mm
Height	620.5 mm
Depth	27 mm
Colour tint	Transparent

Environment

Ambient air temperature for operation	-15...60 °C
---------------------------------------	-------------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information