

1.06/ST

Puller-Set

with stand

Code	ETIM
8111570	EC011834
EAN	UNSPSC
4036976103700	27-11-17-12
Country of origin	eCl@ss
Germany	21-04-15-01
Customs tariff number	
82055980	



Article description

- Consisting of 5 pullers in different sizes with standard or quick-release pulling hook or all-steel hook with hook brake
- Scale for uniform adjustment of the puller legs. Allows centred pulling, with optimised application of force, even when extremely high pulling forces are required
- For clamping depths up to Ø 250 mm external, Ø 330 mm internal, and clamping reach up to 200 mm

Article parts list

1.06/1 Universal puller 2-arm 90x100 mm,1.06/1A Universal puller 2-arm 130x100 mm,1.06/2 Universal puller 2-arm 160x150 mm,1.06/2A Universal puller 2-arm 200x150 mm,1.06/3 Universal puller 2-arm 250x200 mm,1.06/97 Stand empty

Article information

Contents (Qty of pieces)	5	Spindle anti-slip device	no
Graduation	yes	Screws included	no
reversible arms available	no	Anti-slip device on the spindle	no
Clamping bracket available	no	Exchangeable spindle tip	no
Net weight [kg]	19 kg	Can be retrofitted with hydraulic spindle	no
Hook brake available	yes	Clamping width (max.) external pulling [mm]	250 mm
Hook can be moved parallel	no	Clamping width a2 (max.) internal pulling [mm]	330 mm
Quick release lever available	yes	Usable clamping reach	bis 200 mm
3D data available	no		