

axial kit EAMM-A-D32-42A

Part number: 543148

☆ Core product range

Suitable for electric drives.

FESTO



Data sheet

Feature	Value
Assembly position	Any
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	1.1 Nm
Product weight	140 g
Interface code, actuator	D32A D32B D32C
Interface code, motor in	42A
Materials note	Contains PWIS substances Conforms to RoHS