

TS800N

24 Hour Compact Plug-In Time Controller

Features & Benefits

- Easy to use setting pins
- 30 minute minimum switching interval
- Interval can be increased in 15 minute steps
- Up to 24 ON & OFF programmes per day (additional pins required)
- Manual override until next programme change



Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Plug-in
Earth Class Rating	Class I
Operating Temperature	0°C to 40°C
Ingress Protection Rating	IP20
Setting Type	Setting Pins
Program Modes	24 Hour
Switch type	Single Pole
Standby Consumption	<1W
Switch rating	13A Resistive, 80W LED, 400W Halogen, 60W CFL
Shortest Switching Time	30 Minutes

Data sheet

TS800N

Time / Time Controllers

General

Weight (g)	116
Height (mm)	73
Width (mm)	73
Depth (mm)	67
Body Construction	Polycarbonate
Product Colour	White
EAN Number	5012483013397
Guarantee Period	3 Years

Line Diagrams

