

Han® S 120 MC screw-in M6



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 000 8161
Specification	Han® S 120 MC screw-in M6
HARTING eCatalogue	https://harting.com/09930008161

Identification

Category	Contacts
Series	Han® S
Identification	Han® S 120
Type of contact	Screw-in contact
Description of the contact	Male M6

Version

Termination method	Screw termination
--------------------	-------------------

Technical characteristics

Rated current	≤120 A
Contact resistance	≤0.3 mΩ

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained



Pushing Performance
Since 1945

Material properties

Fire protection on railway vehicles EN 45545-2 (2020-08) + A1 (2023-10)

Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	2
Net weight	22.88 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140188723
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522