


Datasheet

ENGLISH

Midget Groove LED Indicator Lamp

RS Stock number 204-265

Dimensions (mm):



Specifications:

LED/Multiled	LED
Mounting Size	TI ¾
Mounting Finish	-
Protection	-
Mount Holder	Midget Groove
Chip Qty	1
Indicator Colour	Red
Optimum Voltage (V)	12V ac/dc
Rectifier	Half Wave

AC Current	7mA
DC Current	15mA
Voltage Tolerance	10%
Optimum Temperature	-30°C +60°C
Storage Temperature	-30°C+60°C
Contact Tab	Midget Groove
Wavelength (nm)	630
Intensity	1750mcd

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.