



ENGLISH

Datasheet

RS Pro Pro REX Slim 300W LED Floodlight Black

RS Stock No: 176-8526



This RS Pro 300W LED Floodlight has an ultra slim line body for an aesthetically pleasing look and discrete installation.

It is ideal for industrial and commercial applications, it is a suitable replacement for 600W HID Fittings and is suitable for outdoor use. It comes with an angled bracket and 1.5m of flex for easier installs.



ENGLISH

Typical Properties

| | |
|--------------------|-----------------------------|
| Material | Aluminium & Toughened Glass |
| Wattage | 300 W |
| Beam Angle | 115° |
| Lumen Output | 27,000 Lm |
| Lumen Efficiency | 90 Lm/W |
| Lamp Type | Fixed LED |
| Voltage | 220-240 V AC / 50-60Hz |
| Colour Temperature | Cool White |
| CCT | 4000K |
| IP Rating | IP65 |
| IK Rating | IK08 |
| Rated Life | 30,000hrs |

