

Han TC100 female contact M5



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 6628
Specification	Han TC100 female contact M5
HARTING eCatalogue	https://harting.com/09110006628

Identification

Category	Contacts
Series	TC 100
Type of contact	Screw contact
Description of the contact	M5

Version

Termination method	Screw termination
Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Rated current	≤100 A
Contact resistance	≤0.3 mΩ
Tightening torque	2.5 Nm
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated



Pushing Performance
Since 1945

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	10
Net weight	31.21 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140572966
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522