

TRADE 3-PART SKYMASTER LADDER - Data sheet

One ladder - six functions



- Top section with rung hooks and locking mechanism.
- Strong nylon straps with sewn-in fixing tab.
- Sturdy, screwed fittings made from extruded section.
- Optimum guide connection that encompasses the whole stile.
- Locking mechanism and guides are bolted in so that they can be replaced.
- High-strength ZARGES quality flanged connection between rung and stile.
- Replaceable 2-component plastic end caps ensure positioning without risk of slipping and at the same time provide firm seating in the stile.
- Rungs and stiles made from extruded aluminium sections.
- Can be used on steps / stairs.

A wealth of functionality at comparatively little expense.

- Wide crosspiece stabiliser bar

Dimensions table

RS article number	No of rungs	Closed length (m)	2-part ext. Length (m) *	3-part ext. Length (m)	Weight (kg)
6693526	3 x 7	2.20	3.60	5.00	15.0

* Also known as free standing height



 **ZARGES**