



Datasheet

RS PRO Automatic cable reel H05RR-F 3G1.5mm² 16(15.6+0.4)+2(1.7+0.3)m,Schuko IP44

Stock number: 171-7877





Electrical Specification:

Rated voltage: 230 V ac 50Hz Rated power (Full-reeled): 1000W Rated power (Unreeled): 3500W

Re-settable thermal protection @56+/-5°C

Special Feature:

Heavy duty industrial cable reel with spring load.

High quality engineer PP housing . Plug and Socket Type : Schuko Degree of protection: IP44

Input line: $H05RR-F,3G1.5mm^2,2m$ length (1.7m net cable length,0.3M cable inside cable reel) . Output line: $H05RR-F,3G1.5mm^2,16m$ length (15.6m net cable length,0.4M cable inside cable reel) .

Pull the power cords and stop some location as you want.

Wall bracket 180 degree swivel.

Over current or temperature protector.

Dimensions: 380x163x330mm