



## Bulkhead Polycarbonate Lens White



- Bulkhead suitable for commercial applications (supplied less lamp)
- Aluminium alloy body to prevent corrosion
- Option of vandal resistant polycarbonate or glass lens

### General Information

Lamp Type	E27
IP Rating	IP65
IK Rating	IK07
Class Protection	1
Internal / External	Internal / External
Surface / Recessed / Suspended	Surface
Warranty (Years)	4
Material	Aluminium, Polycarbonate

### Technical Information

Wattage	100W
Operating Temp	0°C to 25°C



