



ENGLISH

Datasheet

RS Pro 20W iSpot Frameless CCT Floodlight + PIR

RS Stock No: 188-3494



This RS Pro 20W iSpot Frameless CCT Floodlight + PIR is ideal for residential applications such as houses, driveways, patios, car parks and garages. CCT function with supplied remote control. Incorporates air breath technology, allowing continuous ventilation to maintain pressure balance of floodlight against outdoor environment. Angled bracket and 0.5m of power flex for easy installation.



Typical Properties

ENGLISH

Material	Die-cast Aluminium, Toughened Glass
Wattage	20W
Supply Voltage	220 – 240AC, 50-60Hz
Power Factor	≥0.9
Colour Temperature	3000/4000/5000K Warm White/Cool White/Daylight
Light Colour	
Lumens	1800 Lm
Luminous Efficiency	90Lm/W
Colour Rendering Index	Ra ≥70
Beam Angle	110°
Replaceable LED's	No
Dimmable	No
IP Rating	IP65
Rated Life	30,000 Hours
Warranty	3 Years

