



---

**PRODUCT-DETAILS**

# SPUL16/50M

## 16MM GS-PVC COAT CONDUIT 50M - GR



---

**General Information**

<b>Extended Product Type:</b>	SPUL16/50M
<b>Product ID:</b>	7TCA296030R0366
<b>EAN:</b>	5020963004551
<b>Catalog Description:</b>	16MM GS-PVC COAT CONDUIT 50M - GR
<b>Long Description:</b>	Liquid Tight, Medium Flexibility, Covered Steel Conduit, Nominal Conduit Size 16mm, Outside Diameter 17.8mm, Inside Diameter 12.8mm, Static Bend Radius 50mm, Reel Length 50 Meters, UL Listed and CSA Approved, PVC Covered Galvanised Steel Core with Copper Packing, Grey
<b>Display Name:</b>	SPUL16/50M

---

**Additional Information**

<b>Product Main Type:</b>	Adaptaflex Flexible Cable Protection
<b>Application:</b>	Flexible Protection Systems

---

**Ordering**

---

EAN: 5020963004551

UPC: 786210275307

---

## Dimensions

---

Outside Diameter: 17.8 mm

---

## Technical

---

Number of Batteries: 0

Color: Gray

Material: Galvanized Steel Core with PVC Cover and Copper Packing

---

## Environmental

---

WEEE Category: Product Not in WEEE Scope

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

---

## Container Information

---

Package Level 1 Units: 1 piece

Package Level 1 EAN: 5020963004551

Package Level 1 Height: 9.37 in  
238 mm

Package Level 1 Depth / Length: 19.25 in  
489 mm

Package Level 1 Width: 19.25 in  
489 mm

---

## Certificates and Declarations

---

Declaration of Conformity - CE: 9AKK107492A9618

RoHS Declaration: 9AKK107992A8994

REACH Declaration: 9AKK107992A8994

---

## External Classifications and Standards

---

ETIM 8: EC001179 - Protective metallic hose

ETIM 9: EC001179 - Protective metallic hose

UNSPSC: 39131706

---

## Categories

---

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

