

T 12/1

Versatile, robust and tilt-proof dry vacuum cleaner T 12/1 with superb suction power. It is particularly quiet and manoeuvrable and on request is available with HEPA filter.



Order no. 1.355-100.0

- Clip system
- Foldable cable hook
- Operation using foot switch

Technical data		
EAN code		4039784723320
Supply voltage	Ph / V / Hz	1 / 220 - 240 / 50 - 60
Vacuum	mbar / kPa	220 / 22
Air flow	l/s	43
Rated performance	W	700
Container content	l	12
Standard nominal width		ID 35
Cable length	m	12
Sound pressure level	dB(A)	60
Weight without accessories	kg	6.4
Weight incl. packaging	kg	9.6
Dimensions (L × W × H)	mm	410 × 315 × 340

Equipment		
Suction hose	m	2 / with bend
Suction tube	piece(s) × m	2 × 0.5 / Metal
Motor protection filters	piece(s)	1
Filter bag	piece(s)	1 / Fleece
Combi floor nozzle		■
Container material		Plastic
Clip system for extending hose		■
Protection class		II
Permanent filter basket		Nylon

■ Included in the scope of supply.



Highly effective HEPA-13 filter

- The optional HEPA filter ensures particle-free, hygienically clean outgoing air.
- High filtration and separation degree of 99.95% withholds tiny particles.
- Certified in accordance with test standard DIN EN 1822:2019.



On-board cord storage

- The power cable is always stored safely for transport.



Main filter basket

- Large, washable permanent main filter for optimal dust separation.
- Machine operation is possible both with and without filter bag.

ACCESSORIES FOR T 12/1

1.355-100.0



		Order no.	Description	
FILTER T/ NT				
Main filter baskets				
Permanent main filter basket, T 12/1, T 15/1, T 17/1	1	5.731-640.0	Main filter basket for T 15/1, T 12/1 and T 17/1 can be used as a main filter with or without filter bag. Nylon-plastic frame, washable up to 40°C.	■
	2	4.731-011.0	Plastic frames with reinforced fleece material, washably to 40°C.	□
HEPA Filter				
HEPA 13 filter, packaged	3	6.414-080.0	HEPA 13 filter with 99.95% separation degree certified according to test standard DIN EN 1822:2019. For increasing the filter capacity and improving the blower air.	□
Fabric filter bag				
Fabric filter bag	4	6.904-316.0	The fabric filter bag for Kärcher dry vacuum cleaners is made of cotton and can be washed at up to 40 °C.	□
Exhaust air filter				
Standard exhaust air filter, 3 × , BV 5/1, BV 5/1 Bp, T 12, T 15, T 17	5	6.414-802.0	Standard exhaust filter and diffusor for reducing filtered air. Made of foam.	□
Motor protection filter, 3 × , BV 5/1, T 7, T 8, T 9, T 10, T 12, T 15	6	2.889-119.0	Motor protection filter, removable fleece, which can be replaced when heavily soiled.	□
Filter foam, 3 × , BV 5/1, T 7, T 10, T 12, T 15	7	4.414-015.0	Efficient exhaust filter made from PES fleece material (filter foam) in size 128 × 97 mm. Package content: Pack of 3.	□
BENDS				
Bend, plastic				
Bend with air-flow regulator, T, DN 35, plastic, antistatic, clip 2.0 at hose end, cone at accessory end	8	2.889-148.0	Antistatic, ergonomic bends with air-flow regulator in size DN 35 for dry vacuum cleaners. Equipped with a clip 2.0 connection at the hose end and a cone connection at the accessory end.	■
SUCTION NOZZLES				
Combi-nozzles, dry				
Combi-nozzle, DN 35, 280 mm	9	2.889-129.0	Plastic floor nozzle, ID 35 and switchable.	■
Parquet nozzle, DN 35, 360 mm	10	2.889-196.0	Parquet nozzle with wide working width	□
Parquet nozzle, DN 35, 300 mm	11	2.889-197.0		□
Floor nozzles				
Floor nozzle for dry vacuum cleaner DN 35, 290 mm wide	12	2.889-360.0	High-quality and versatile floor nozzle in DN 35. With practical parking hook for cleaning textile and hard floors with dry vacuum cleaners from Kärcher. Width: 290 mm.	□
Crevice nozzles				
Crevice nozzle, DN 35, plastic, 210 mm	13	2.889-130.0	Plastic crevice nozzle.	□
Upholstery nozzles				
Upholstery nozzle DN 35	14	6.905-998.0	Plastic upholstery nozzle in DN 35.	□

■ Included in the scope of supply. □ Available accessories.

ACCESSORIES FOR T 12/1

1.355-100.0



		Order no.	Description	
SUCTION NOZZLES				
Suction brushes				
Suction brush DN 35	15	2.889-221.0	Suction brush DN 35 with horsehair natural bristles.	<input type="checkbox"/>
Turbo nozzles				
Turbo upholstery nozzle	16	2.860-113.0	Plastic turbo upholstery nozzle (DN 35/32, 160 mm) with reduction sleeve.	<input type="checkbox"/>
Turbo floor nozzle	17	2.860-114.0	Plastic turbo floor nozzle (DN 35/32, 270 mm) with reduction sleeve.	<input type="checkbox"/>
SUCTION TUBES				
Suction tubes, metal				
Suction tube, chrome-plated	18	6.902-074.0	Suction tube, metal, chrome-plated, NW 35. Length: 0.5 metres.	<input checked="" type="checkbox"/>
SUCTION HOSES				
Suction hoses with clip system 2.0 (compatible with vacuum cleaners from model year 2017 on)				
Suction hose, T, DN 35, length 2 m, Clip 2.0, click fastener	19	2.889-161.0	The suction hose in nominal width DN 35 and with 2 m length is suitable for use with dry vacuum cleaners from Kärcher.	<input checked="" type="checkbox"/>
Extension hose, T and NT, DN 35, length 2.5 m, electrically conductive, clip 2.0, connecting adapter	20	2.889-343.0	The electrically conductive extension hose in nominal width DN 35 and with 2.5 m length is suitable for use with wet and dry vacuum cleaners.	<input type="checkbox"/>
Hose connection				
Adapter, ID 32/35, with internal thread	21	6.902-077.0	Electrically non-conductive adapter with internal thread. For connecting two suction hoses without connectors. Suitable for DN 32 or DN 35.	<input type="checkbox"/>
NOZZLE KITS				
DN 35 nozzle kit: crevice nozzle, upholstery nozzle, suction brush	22	2.860-116.0	Nozzle kit consisting of a crevice nozzle, upholstery nozzle and suction brush. The nozzle kit is suitable for all Kärcher dry vacuum cleaners and wet and dry vacuum cleaners in nominal width DN 35.	<input type="checkbox"/>
OTHER ACCESSORIES NT				
Adapter clip new on clip old DN 35	23	2.889-312.0	Adapter for connection of hoses of the new accessory system of dry and wet and dry vacuum cleaners to bends or extension hoses of the old system. For nominal width DN 35.	<input type="checkbox"/>
FURTHER ACCESSORIES DRY VACUUM CLEANERS				
Repair set Kaercher NW35	24	2.639-329.0	Repair kit for dry vacuum cleaner accessories in DN 35. The kit includes a threaded and clamping ring, a connecting adapter, as well as a seal.	<input type="checkbox"/>
FILTER BAGS				
Fleece filter bags				
Fleece filter bags, 10 × , T 10, T 12, Trek Vac 2, Trek Vac 3	25	6.904-315.0	Extremely tear-resistant, 3-ply fleece filter bags, dust class M. Fleece filter bags have 2 to 3 times the capacity of conventional paper filter bags. Standard for T 10/1 and T 12/1.	<input type="checkbox"/>
Fleece filter bags, 200 × , T 10, T 12, Trek Vac 2, Trek Vac 3	26	6.904-321.0	Fleece filter bag, 3-ply, tear-proof, dust class M, large-scale consumer unit.	<input type="checkbox"/>
Paper filter bags				
Paper filter bags, 10 × , T 12/1	27	6.904-312.0	10 paper filter bags dust class M. Suitable for all T 12/1 models.	<input type="checkbox"/>
Paper filter bags, 200 × , T 12/1	28	6.904-318.0	Dust class M	<input type="checkbox"/>

■ Included in the scope of supply. □ Available accessories.

ACCESSORIES FOR T 12/1

1.355-100.0



		Order no.	Description	
CONNECTING SLEEVES				
Expansion pieces (tube -> nozzle)				
Adapter	29	6.902-083.0	From DN 32 to DN 35: Plastic adapter (electrically non-conductive). Suitable for BV and T vacuum cleaners.	<input type="checkbox"/>
Reducing sleeves				
Reducer from ID 35 to ID 32	30	6.902-072.0	Reducer with internal connecting cone DN 32. Ideal for accessories from the industrial vacuum cleaner range in combination with industrial NT vacuum cleaners.	<input type="checkbox"/>
Reduction/expansion adapter kit				
Set of reducers / adapter sleeves	31	2.860-117.0	DN 40/35, DN 35/32 (tube -> nozzle), plastic.	<input type="checkbox"/>

■ Included in the scope of supply. □ Available accessories.