

Path: [Home](#) > [Enclosure Index](#) > Extruded Aluminum w/ **Metal** End Panels



(click to enlarge)

**Black Anodized  
(Open View)**



(click to enlarge)

**Black Anodized  
(Assembled View)**



(click to enlarge)


**Blue Anodized  
(Assembled View)**



(click to enlarge)











**Clear Anodized  
(Assembled View)**







































































































### Key Features:







- Designed to house P.C. boards or for equipment interfacing.
- Sized for standard Eurocards.
- P.C. boards mount horizontally by sliding into internal slots extruded into the enclosure body.
- Rugged body constructed from extruded aluminum with a minimum thickness of .06" (1.5 mm).
- Extruded body includes a slide removable "belly" plate - except in smaller "C" & "D" sizes (ie..1455D601, 1455D801, 1455C801 & 1455C1201 sizes)
- See  "[photo tables](#)" for more visual details.

### Includes:

- Two aluminum end panels - finish matched to extruded aluminum body (or link here if you prefer our solid [plastic end panel version](#))
- Two black ABS plastic bezels (your option to install)
- Extruded aluminum body - choice of clear, black or blue anodized finish
- Self adhesive rubber feet.
- All hardware - end panel screws are #6 x 3/8" TTT - thread rolling, steel screws with a #4 flat head phillips drive. Zinc plate finish - either clear or black (black screws are used on the both the black & blue models).
- For black replacement screws (quantity 100) order part number **1455MS100BK**
- For clear replacement screws (quantity 100) order part number **1455MS100**
- **NOTE:** Recommended screw torque is 5 lbf/in

Part Number	Anodized Color	 Reader File	AutoCAD .dwg Files (zipped)	3D Solid Model .igs & .stp files (zipped)	Units	Length	Width	Height
<b>1455D601</b> <b>1455D601BK</b> <b>1455D601BU</b>	Clear	 209K	 172K	 206K	Inches	2.36	1.76	0.99
	Black				mm	60	45	25
<b>1455D801</b> <b>1455D801BK</b> <b>1455D801BU</b>	Clear	 209K	 172K	 206K	Inches	3.15	1.76	0.99
	Black				mm	80	45	25
<b>1455C801</b> <b>1455C801BK</b>	Clear	 193K	 167K	 154K	Inches	3.15	2.13	0.91
	Black				mm	80	54	23

<b>1455C801BU</b>	Blue							
<b>1455C1201</b>	Clear				Inches	4.72	2.13	0.91
<b>1455C1201BK</b>	Black				mm	120	54	23
<b>1455C1201BU</b>	Blue	195K	167K	154K				
<b>1455J1201</b>	Clear				Inches	4.72	3.07	1.06
<b>1455J1201BK</b>	Black				mm	120	78	27
<b>1455J1201BU</b>	Blue	269K	159K	237K				
<b>1455K1201</b>	Clear				Inches	4.72	3.07	1.69
<b>1455K1201BK</b>	Black				mm	120	78	43
<b>1455K1201BU</b>	Blue	197K	174K	213K				
<b>1455L1201</b>	Clear				Inches	4.72	4.06	1.20
<b>1455L1201BK</b>	Black				mm	120	103	30.5
<b>1455L1201BU</b>	Blue	273K	158K	227K				
<b>1455N1201</b>	Clear				Inches	4.72	4.06	2.09
<b>1455N1201BK</b>	Black				mm	120	103	53
<b>1455N1201BU</b>	Blue	173K	175K	230K				
<b>1455J1601</b>	Clear				Inches	6.30	3.07	1.06
<b>1455J1601BK</b>	Black				mm	160	78	27
<b>1455J1601BU</b>	Blue	270K	155K	237K				
<b>1455K1601</b>	Clear				Inches	6.30	3.07	1.69
<b>1455K1601BK</b>	Black				mm	160	78	43
<b>1455K1601BU</b>	Blue	216K	175K	214K				
<b>1455L1601</b>	Clear				Inches	6.30	4.06	1.20
<b>1455L1601BK</b>	Black				mm	160	103	30.5
<b>1455L1601BU</b>	Blue	269K	162K	240K				
<b>1455N1601</b>	Clear				Inches	6.30	4.06	2.09
<b>1455N1601BK</b>	Black				mm	160	103	53
<b>1455N1601BU</b>	Blue	172K	173K	230K				
<b>1455P1601</b>	Clear				Inches	6.30	4.92	1.20
<b>1455P1601BK</b>	Black				mm	160	125	30.5
<b>1455P1601BU</b>	Blue	266K	161K	250K				
<b>1455Q1601</b>	Clear				Inches	6.30	4.92	2.03
<b>1455Q1601BK</b>	Black				mm	160	125	51.5
<b>1455Q1601BU</b>	Blue	271K	164K	291K				
<b>1455R1601</b>	Clear				Inches	6.30	6.50	1.20
<b>1455R1601BK</b>	Black				mm	160	165	30.5
<b>1455R1601BU</b>	Blue	201K	179K	264K				
<b>1455T1601</b>	Clear				Inches	6.30	6.50	2.03
<b>1455T1601BK</b>	Black				mm	160	165	51.5
<b>1455T1601BU</b>	Blue	151K	183K	298K				
<b>1455L2201</b>	Clear				Inches	8.66	4.06	1.20
<b>1455L2201BK</b>	Black				mm	220	103	30.5
<b>1455L2201BU</b>	Blue	261K	161K	240K				
<b>1455N2201</b>	Clear				Inches	8.66	4.06	2.09
<b>1455N2201BK</b>	Black				mm	220	103	53
<b>1455N2201BU</b>	Blue	200K	178K	230K				
<b>1455P2201</b>	Clear				Inches	8.66	4.92	1.20
<b>1455P2201BK</b>	Black				mm	220	125	30.5
<b>1455P2201BU</b>	Blue	261K	163K	250K				
<b>1455Q2201</b>	Clear				Inches	8.66	4.92	2.03
<b>1455Q2201BK</b>	Black				mm	220	125	51.5
<b>1455Q2201BU</b>	Blue	274K	164K	291K				
<b>1455R2201</b>	Clear				Inches	8.66	6.50	1.20

<b>1455R2201BK</b> <b>1455R2201BU</b>	Black Blue	 204K	 178K	 264K	mm	220	165	30.5
<b>1455T2201</b> <b>1455T2201BK</b> <b>1455T2201BU</b>	Clear Black Blue	 155K	 194K	 298K	Inches mm	8.66 220	6.50 165	2.03 51.5

 [Link here to photo tables](#) of each part number

### Color Options:



(click to enlarge)



(click to enlarge)

- Choose either black anodized or clear anodized or blue anodized
- Note that aluminum front & back panels match the enclosure color

## Accessories

### Wallmount Options:
















(click to enlarge)



(click to enlarge)

- Designed to convert these enclosures where shelf or wall mounting is required
- Flanges are .064" (1.6 mm) thick aluminum foot "L" brackets and attach to each end, replacing the aluminum end panels
- Finish available in both clear & black anodized to match enclosure
- **SOLD IN PAIRS**

Part Number	Color	 Reader File	AutoCAD .dwg Files (zipped)	3D Solid Model .igs & .stp files (zipped)	USE WITH ENCLOSURE
<b>1455CF</b> <b>1455CFBK</b>	Clear Black	 142K	 94K	 24K	Any part above starting with 1455C
<b>1455JF</b> <b>1455JFBK</b>	Clear Black	 174K	 83K	 25K	Any part above starting with 1455J
<b>1455KF</b> <b>1455KFBK</b>	Clear Black	 159K	 118K	 23K	Any part above starting with 1455K
<b>1455LF</b> <b>1455LFBK</b>	Clear Black	 159K	 118K	 23K	Any part above starting with 1455L

		160K	110K	25K	
<b>1455NF</b> <b>1455NFBK</b>	Clear Black	 165K	 111K	 25K	Any part above starting with 1455N
<b>1455PF</b> <b>1455PFBK</b>	Clear Black	 180K	 112K	 87K	Any part above starting with 1455P
<b>1455QF</b> <b>1455QFBK</b>	Clear Black	 145K	 113K	 25K	Any part above starting with 1455Q
<b>1455RF</b> <b>1455RFBK</b>	Clear Black	 143K	 111K	 25K	Any part above starting with 1455R
<b>1455TF</b> <b>1455TFBK</b>	Clear Black	 150K	 111K	 25K	Any part above starting with 1455T

**Replacement Parts & Bezel Options:**



(click to enlarge)



(click to enlarge)



(click to enlarge)



(click to enlarge)

**Aluminum Clear End Plate**

**Aluminum Black End Plate**

**Aluminum Blue End Plate**

**Black Plastic - Open Bezel**

USE WITH (Enclosure Part Number)	Aluminum Clear End Plate (10 Pack)	Aluminum Black End Plate (10 Pack)	Aluminum Blue End Plate (10 Pack)	Black Plastic Open Bezel	
				(2 Pack)	(10 Pack)
1455D601	<b>1455DAL-10</b>	<b>1455DALBK-10</b>	<b>1455DALBU-10</b>	<b>1455DBBK</b>	<b>1455DBBK-10</b>
1455D801	<b>1455DAL-10</b>	<b>1455DALBK-10</b>	<b>1455DALBU-10</b>	<b>1455DBBK</b>	<b>1455DBBK-10</b>
1455C801	<b>1455CAL-10</b>	<b>1455CALBK-10</b>	<b>1455CALBU-10</b>	<b>1455CBBK</b>	<b>1455CBBK-10</b>
1455C1201	<b>1455CAL-10</b>	<b>1455CALBK-10</b>	<b>1455CALBU-10</b>	<b>1455CBBK</b>	<b>1455CBBK-10</b>
1455J1201	<b>1455JAL-10</b>	<b>1455JALBK-10</b>	<b>1455JALBU-10</b>	<b>1455JBBK</b>	<b>1455JBBK-10</b>
1455K1201	<b>1455KAL-10</b>	<b>1455KALBK-10</b>	<b>1455KALBU-10</b>	<b>1455KBBK</b>	<b>1455KBBK-10</b>
1455L1201	<b>1455LAL-10</b>	<b>1455LALBK-10</b>	<b>1455LALBU-10</b>	<b>1455LBBK</b>	<b>1455LBBK-10</b>
1455N1201	<b>1455NAL-10</b>	<b>1455NALBK-10</b>	<b>1455NALBU-10</b>	<b>1455NBBK</b>	<b>1455NBBK-10</b>
1455J1601	<b>1455JAL-10</b>	<b>1455JALBK-10</b>	<b>1455JALBU-10</b>	<b>1455JBBK</b>	<b>1455JBBK-10</b>
1455K1601	<b>1455KAL-10</b>	<b>1455KALBK-10</b>	<b>1455KALBU-10</b>	<b>1455KBBK</b>	<b>1455KBBK-10</b>
1455L1601	<b>1455LAL-10</b>	<b>1455LALBK-10</b>	<b>1455LALBU-10</b>	<b>1455LBBK</b>	<b>1455LBBK-10</b>
1455N1601	<b>1455NAL-10</b>	<b>1455NALBK-10</b>	<b>1455NALBU-10</b>	<b>1455NBBK</b>	<b>1455NBBK-10</b>
1455P1601	<b>1455PAL-10</b>	<b>1455PALBK-10</b>	<b>1455PALBU-10</b>	<b>1455PBBK</b>	<b>1455PBBK-10</b>
1455Q1601	<b>1455QAL-10</b>	<b>1455QALBK-10</b>	<b>1455QALBU-10</b>	<b>1455QBBK</b>	<b>1455QBBK-10</b>
1455R1601	<b>1455RAL-10</b>	<b>1455RALBK-10</b>	<b>1455RALBU-10</b>	<b>1455RBBK</b>	<b>1455RBBK-10</b>
1455T1601	<b>1455TAL-10</b>	<b>1455TALBK-10</b>	<b>1455TALBU-10</b>	<b>1455TBBK</b>	<b>1455TBBK-10</b>
1455L2201	<b>1455LAL-10</b>	<b>1455LALBK-10</b>	<b>1455LALBU-10</b>	<b>1455LBBK</b>	<b>1455LBBK-10</b>
1455N2201	<b>1455NAL-10</b>	<b>1455NALBK-10</b>	<b>1455NALBU-10</b>	<b>1455NBBK</b>	<b>1455NBBK-10</b>
1455P2201	<b>1455PAL-10</b>	<b>1455PALBK-10</b>	<b>1455PALBU-10</b>	<b>1455PBBK</b>	<b>1455PBBK-10</b>
1455Q2201	<b>1455QAL-10</b>	<b>1455QALBK-10</b>	<b>1455QALBU-10</b>	<b>1455QBBK</b>	<b>1455QBBK-10</b>



1455R2201	<a href="#">1455RAL-10</a>	<a href="#">1455RALBK-10</a>	<a href="#">1455RALBU-10</a>	<a href="#">1455RBBK</a>	<a href="#">1455RBBK-10</a>
1455T2201	<a href="#">1455TAL-10</a>	<a href="#">1455TALBK-10</a>	<a href="#">1455TALBU-10</a>	<a href="#">1455TBBK</a>	<a href="#">1455TBBK-10</a>



(click to enlarge)

**Red ABS Plastic - Open Bezel**



(click to enlarge)

**Yellow ABS Plastic - Open Bezel**

USE WITH (Enclosure Part Number)	Red		Yellow	
	(2 Pack)	(10 Pack)	(2 Pack)	(10 Pack)
1455C801	<a href="#">1455CBRED</a>	<a href="#">1455CBRED-10</a>	<a href="#">1455CBY</a>	<a href="#">1455CBY-10</a>
1455C1201	<a href="#">1455CBRED</a>	<a href="#">1455CBRED-10</a>	<a href="#">1455CBY</a>	<a href="#">1455CBY-10</a>
1455J1201	<a href="#">1455JBRED</a>	<a href="#">1455JBRED-10</a>	<a href="#">1455JBY</a>	<a href="#">1455JBY-10</a>
1455K1201	<a href="#">1455KBRED</a>	<a href="#">1455KBRED-10</a>	<a href="#">1455KBY</a>	<a href="#">1455KBY-10</a>
1455L1201	<a href="#">1455LBRED</a>	<a href="#">1455LBRED-10</a>	<a href="#">1455LBY</a>	<a href="#">1455LBY-10</a>
1455N1201	<a href="#">1455NBRED</a>	<a href="#">1455NBRED-10</a>	<a href="#">1455NBY</a>	<a href="#">1455NBY-10</a>
1455J1601	<a href="#">1455JBRED</a>	<a href="#">1455JBRED-10</a>	<a href="#">1455JBY</a>	<a href="#">1455JBY-10</a>
1455K1601	<a href="#">1455KBRED</a>	<a href="#">1455KBRED-10</a>	<a href="#">1455KBY</a>	<a href="#">1455KBY-10</a>
1455L1601	<a href="#">1455LBRED</a>	<a href="#">1455LBRED-10</a>	<a href="#">1455LBY</a>	<a href="#">1455LBY-10</a>
1455N1601	<a href="#">1455NBRED</a>	<a href="#">1455NBRED-10</a>	<a href="#">1455NBY</a>	<a href="#">1455NBY-10</a>
1455P1601	<a href="#">1455PBRED</a>	<a href="#">1455PBRED-10</a>	<a href="#">1455PBY</a>	<a href="#">1455PBY-10</a>
1455Q1601	<a href="#">1455QBRED</a>	<a href="#">1455QBRED-10</a>	<a href="#">1455QBY</a>	<a href="#">1455QBY-10</a>
1455R1601	<a href="#">1455RBRED</a>	<a href="#">1455RBRED-10</a>	<a href="#">1455RBY</a>	<a href="#">1455RBY-10</a>
1455T1601	<a href="#">1455TBRED</a>	<a href="#">1455TBRED-10</a>	<a href="#">1455TBY</a>	<a href="#">1455TBY-10</a>
1455L2201	<a href="#">1455LBRED</a>	<a href="#">1455LBRED-10</a>	<a href="#">1455LBY</a>	<a href="#">1455LBY-10</a>
1455N2201	<a href="#">1455NBRED</a>	<a href="#">1455NBRED-10</a>	<a href="#">1455NBY</a>	<a href="#">1455NBY-10</a>
1455P2201	<a href="#">1455PBRED</a>	<a href="#">1455PBRED-10</a>	<a href="#">1455PBY</a>	<a href="#">1455PBY-10</a>
1455Q2201	<a href="#">1455QBRED</a>	<a href="#">1455QBRED-10</a>	<a href="#">1455QBY</a>	<a href="#">1455QBY-10</a>
1455R2201	<a href="#">1455RBRED</a>	<a href="#">1455RBRED-10</a>	<a href="#">1455RBY</a>	<a href="#">1455RBY-10</a>
1455T2201	<a href="#">1455TBRED</a>	<a href="#">1455TBRED-10</a>	<a href="#">1455TBY</a>	<a href="#">1455TBY-10</a>



(click to enlarge)



(click to enlarge)



(click to enlarge)

**Translucent Blue  
Polycarbonate - Open Bezel**



(click to enlarge)

**Translucent (IR) Red  
Polycarbonate - Open Bezel**

USE WITH (Enclosure Part Number)	Translucent Blue		Translucent Red	
	(2 Pack)	(10 Pack)	(2 Pack)	(10 Pack)
1455C801	<a href="#">1455CBTBU</a>	<a href="#">1455CBTBU-10</a>	<a href="#">1455CBTRD</a>	<a href="#">1455CBTRD-10</a>
1455C1201	<a href="#">1455CBTBU</a>	<a href="#">1455CBTBU-10</a>	<a href="#">1455CBTRD</a>	<a href="#">1455CBTRD-10</a>
1455J1201	<a href="#">1455JBTBU</a>	<a href="#">1455JBTBU-10</a>	<a href="#">1455JBTRD</a>	<a href="#">1455JBTRD-10</a>
1455K1201	<a href="#">1455KBTBU</a>	<a href="#">1455KBTBU-10</a>	<a href="#">1455KBTRD</a>	<a href="#">1455KBTRD-10</a>
1455L1201	<a href="#">1455LBTBU</a>	<a href="#">1455LBTBU-10</a>	<a href="#">1455LBTRD</a>	<a href="#">1455LBTRD-10</a>
1455N1201	<a href="#">1455NBTBU</a>	<a href="#">1455NBTBU-10</a>	<a href="#">1455NBTRD</a>	<a href="#">1455NBTRD-10</a>
1455J1601	<a href="#">1455JBTBU</a>	<a href="#">1455JBTBU-10</a>	<a href="#">1455JBTRD</a>	<a href="#">1455JBTRD-10</a>
1455K1601	<a href="#">1455KBTBU</a>	<a href="#">1455KBTBU-10</a>	<a href="#">1455KBTRD</a>	<a href="#">1455KBTRD-10</a>
1455L1601	<a href="#">1455LBTBU</a>	<a href="#">1455LBTBU-10</a>	<a href="#">1455LBTRD</a>	<a href="#">1455LBTRD-10</a>
1455N1601	<a href="#">1455NBTBU</a>	<a href="#">1455NBTBU-10</a>	<a href="#">1455NBTRD</a>	<a href="#">1455NBTRD-10</a>
1455P1601	<a href="#">1455PBTBU</a>	<a href="#">1455PBTBU-10</a>	<a href="#">1455PBTRD</a>	<a href="#">1455PBTRD-10</a>
1455Q1601	<a href="#">1455QBTBU</a>	<a href="#">1455QBTBU-10</a>	<a href="#">1455QBTRD</a>	<a href="#">1455QBTRD-10</a>
1455R1601	<a href="#">1455RBTBU</a>	<a href="#">1455RBTBU-10</a>	<a href="#">1455RBTRD</a>	<a href="#">1455RBTRD-10</a>
1455T1601	<a href="#">1455TBTBU</a>	<a href="#">1455TBTBU-10</a>	<a href="#">1455TBTRD</a>	<a href="#">1455TBTRD-10</a>
1455L2201	<a href="#">1455LBTBU</a>	<a href="#">1455LBTBU-10</a>	<a href="#">1455LBTRD</a>	<a href="#">1455LBTRD-10</a>
1455N2201	<a href="#">1455NBTBU</a>	<a href="#">1455NBTBU-10</a>	<a href="#">1455NBTRD</a>	<a href="#">1455NBTRD-10</a>
1455P2201	<a href="#">1455PBTBU</a>	<a href="#">1455PBTBU-10</a>	<a href="#">1455PBTRD</a>	<a href="#">1455PBTRD-10</a>
1455Q2201	<a href="#">1455QBTBU</a>	<a href="#">1455QBTBU-10</a>	<a href="#">1455QBTRD</a>	<a href="#">1455QBTRD-10</a>
1455R2201	<a href="#">1455RBTBU</a>	<a href="#">1455RBTBU-10</a>	<a href="#">1455RBTRD</a>	<a href="#">1455RBTRD-10</a>
1455T2201	<a href="#">1455TBTBU</a>	<a href="#">1455TBTBU-10</a>	<a href="#">1455TBTRD</a>	<a href="#">1455TBTRD-10</a>



catalog pages on this series (193K) [9C-1455.pdf](#)

Exactly what you are looking for???

Link to our stocking distributors - most have "on-line" pricing, stock check and ordering!!!

[Our Distributors](#)

[Order from your favorite distributor](#)

[Home](#) | [Products](#) | [Distributors](#) | [Technical](#) | [Contact Us](#) | [Other Options](#)