

Rapid

Rapid PRO EG380 Industrial Glue Gun

Professional, industrial performance glue gun with an exceptionally high glue output of 2200 g / hour. EG380 is designed for high frequency, demanding usage and precision application. Smart features include a handy, adjustable temperature control (120°-230 °C) for versatile application with different materials and an ergonomic 4-finger handle to reduce effort required. Works with both EVA and polyamide glue, has a 3.5 m rubber cable for optimal access and is supplied with a fixed and a mobile stand.



Attributes

- For 12 mm glue sticks
- 2200 g/h glue output
- Power 400 W
- 1 min at 130 °C, 3 min at 210 °C
- Adjustable temperature 120-230 °C
- Temperature settings : 130 °C, 150 °C, 170 °C, 190 °C, 210 °C and 230 °C
- Works with both EVA and polyamide glue.
- Standard nozzle Ø3.5 mm, exchangeable
- Ergonomic 4-finger handle
- 3.5 meter cord
- Supplied with a fixed and a mobile stand
- 2 year guarantee



Specifications

Number	5000181
Colour	-----
Material	Technical plastic and Metal
Dimensions (W x H x D)	303 x 102 x 380 mm
Adjustable temperature	Yes
Interchangeable nozzles	Yes
Heating time	1 min at 130 °C, 3 min at 210 °C
Glue stick diameter	12 mm
Glue output g/h	2200 g/h
Power W	400 W
Temperature C	120-230 °C
Package content	1
Suitable for	Use for Carton closing, electronic, wood assembly, furniture, cable fixing
Miscellaneous	EG380 220-240V packed in Box , languages : GB, FR, NL,DE, IT,PT,ES,GR, SE,DK,FI, CZ,RU,SI, SK, BG
Weight	1300 g
Packing unit	6
Pallet quantity	54
Minimum order quantity	1
EAN code	4051661007385