
coupling socket KD2-CK-4 Part number: 531622

Self-closing



Data sheet

Feature	Value
Nominal size	2.9 mm
Operating pressure complete temperature range	-0.95 12 bar
Standard nominal flow rate	123 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-10 80 °C
Product weight	16 g
Pneumatic connection, port 1	СК-4
Materials note	Conforms to RoHS

FESTO