



**> VERSATILE  
PROTECTION  
FOR ALL YOUR  
TOUGH JOBS**

**ACTIVARMR<sup>®</sup>**  
PERSONAL PROTECTIVE GEAR

**MULTIPURPOSE GLOVES**

**Ansell**

# > MULTIPURPOSE

## THE RIGHT GLOVES FOR EVERYDAY EXTREMES

**IN GENERAL CONSTRUCTION OR DIY PROJECTS, YOU NEVER KNOW WHAT CHALLENGES THE NEXT JOB MIGHT BRING. YOU NEED PROTECTION AS VERSATILE AS YOU ARE.**

That's where ActivArm<sup>®</sup> Multipurpose gloves come in — the only choice that can truly stand up to it all.

Three different pairs — each with unique, functional aesthetics that convey durability — mean you'll find the right level of protection, dexterity and grip for whatever work the day brings, from the light to the heavyweight. That makes them a great choice for general

contractors and their teams. Each pair is engineered to the core to deliver a level of performance like nothing you've experienced before. Other gloves simply can't compare in long-term wear or ongoing safety. You'll get outstanding protection, while still enjoying the "second skin" feel you need for dexterity and precision all day long, every day.

## >> LIGHT DUTY (97-007)

Even the lightweight jobs can be tough on the hands after a long day. ActivArm<sup>®</sup> Light Duty gloves give just the right level of protection, while providing the ultimate "second skin" feel. Their breathable nylon liner and a foam nitrile outer layer give you the dexterity and grip you need to safely get the job done.



**SIZES:** 8, 9, 10, 11

## IDEAL FOR\*

- Placing insulation
- Painting
- Light maintenance
- Irrigation work
- Handling drywall/Sheetrock



Slip wrist design for comfort

Nylon for durability, breathability and comfort

Foam nitrile for enhanced wet/dry grip

## EN LEVELS

**3** ABRASION LEVEL

**1** CUT LEVEL



\* While these are the most commonly noted tasks, gloves are not limited to them.

## >> MEDIUM DUTY (97-008)

Some projects demand a tougher layer of protection, like when working with rough materials and power tools. With reinforced palm ridges and an advanced layer of DuPont™ Kevlar®, the ActivArm® Medium Duty gloves stand up to harsh abrasions and cuts, while still delivering excellent dexterity and precision so you can work efficiently.



Adjustable wrist closure with pull tab and ID nameplate

DuPont™ Kevlar® provides protection and durability

Foam nitrile for enhanced wet/dry grip

Reinforced ridges offer palm protection



**SIZES:** 8, 9, 10, 11

### IDEAL FOR\*

- Landscaping
- Flooring/Tiling
- Roofing
- Cutting/Sanding/Sawing
- Piping
- General maintenance/ Material handling

### EN LEVELS

**4** ABRASION LEVEL

**2** CUT LEVEL



## >> HEAVY DUTY (97-009)

For the most demanding jobs, you need the absolute toughest protection. These rugged gloves are engineered for the true extremes. With Ansell's patented Intercept Technology® and DuPont™ Kevlar® fibers, they create the ultimate everyday protection from punctures, cuts and abrasions.



Steel  
DuPont™ Kevlar®  
Ansell Fiber Blend



Adjustable wrist closure with pull tab and ID nameplate

Patented Intercept Technology® with stainless steel and DuPont™ Kevlar® to provide maximum protection

Foam nitrile for enhanced wet/dry grip

Reinforced ridges offer palm and knuckle protection



**SIZES:** 8, 9, 10, 11

### IDEAL FOR\*

- Demolition
- Woodwork
- Heavy cutting/Sawing
- Digging
- Handling sheet metal
- Masonry
- Steel work (tying)

### EN LEVELS

**4** ABRASION LEVEL

**4** CUT LEVEL





Ansell is the world's largest manufacturer of protective gloves. We're the recognized leader for products that defend against workplace injuries with exceptional levels of protection against cuts, abrasions, chemicals and other hazards.

Style	Size	Unit Bar Code	Packaging
ActivArmR® Light Duty 97-007	8	00 76490 47774 5	Cartons of 12 pairs
	9	00 76490 47775 2	
	10	00 76490 47776 9	
	11	00 76490 47777 6	
ActivArmR® Medium Duty 97-008	8	00 76490 47770 7	
	9	00 76490 47771 4	
	10	00 76490 47772 1	
	11	00 76490 47773 8	
ActivArmR® Heavy Duty 97-009	8	00 76490 47766 0	
	9	00 76490 47767 7	
	10	00 76490 47768 4	
	11	00 76490 47769 1	



**Ansell Healthcare Europe**  
 Riverside Business Park Block J  
 Boulevard International 55, 1070 Brussels, Belgium  
 Tel. +32 (0) 2 528 74 00 Fax +32 (0) 2 528 74 01  
 E-mail [info@ansell.eu](mailto:info@ansell.eu)

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application. Ansell, ActivArmR® and Intercept Technology® are registered trademarks of Ansell Limited or one of its affiliates. Kevlar® is a trademark of E.I. du Pont de Nemours and Company. © 2012 Ansell Limited. All Rights Reserved. US Patent Pending 61/598,134; and other US and non-US patents pending.