



verso maintenance trolley with 7 drawers / cupboard & top tray with mat. Featuring a robust, fully welded steel housing with double, independent, storage sections, push - pull handles, 100% extension drawers with drawer blocking and 125mm diameter castors. Drawer configuration: 6x 100mm, 1x 125mm (50 kg U.D.L.) and cupboard section with single, reinforced, door and 1 galvanised steel shelf (75kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 7035 light grey. WxDxH: 1300x550x965mm

Breite [mm]: 1300
Tiefe [mm]: 550
Höhe [mm]: 965
Bruttogewicht [kg]: 118.75
EAN-Code: 5039350148624
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Light grey
Main RAL colour	RAL 7035
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	verso
---------------	-------

Schubladen

Number of drawers	7
Drawer load capacity [kg]	50
Drawer height 1 [mm]	100
Drawer height 2 [mm]	100
Drawer height 3 [mm]	100

Drawer height 4 [mm]	100
Drawer height 5 [mm]	100
Drawer height 6 [mm]	100
Drawer height 7 [mm]	125

Schrank, Gehäuse, Werkbank und EAP

Worktop/housing top type	Top tray and mat
Shelf load capacity [kg]	75
Door type	Plain
Door height 1 [mm]	725