

## 30m Coax High Resolution Monitor VGA Video Cable - HD15 M/M

Product ID: MXTMMHQ30M



The MXTMMHQ30M High Resolution VGA Cable (30-meter) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

### Certifications, Reports and Compatibility



### Applications

- Replace a worn-out or missing VGA monitor cable with this high quality, coax VGA cable
- Supports high resolution VGA monitors (1920x1200)
- Create a longer connection between a high resolution VGA display and a desktop PC/video switch than a typical cable length would allow

### Features

- Triple coaxial + twisted-pair wire for crystal clear display
- Durably constructed cable, with high quality HD15 connectors
- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Fire Rating	CMG Rated (General Purpose)
	Number of Conductors	14
	Number of Ferrites	1
<b>Connector(s)</b>	Connector A	1 - VGA (15 pin, High Density D-Sub) Male
	Connector B	1 - VGA (15 pin, High Density D-Sub) Male
<b>Environmental</b>	Humidity	0 - 80 %RH
	Operating Temperature	0 to 60 °C
	Storage Temperature	-20 to 80 °C
<b>Physical Characteristics</b>	Cable Length	30 m [98.4 ft]
	Color	Black
	Product Length	30 m [98.4 ft]
	Weight of Product	2.7 kg [6 lb]
	Wire Gauge	28 AWG
<b>Packaging Information</b>	Package Height	81 mm [3.2 in]
	Package Length	46 cm [18.1 in]
	Package Quantity	1
	Package Width	35 cm [13.8 in]
	Shipping (Package) Weight	2.8 kg [6.1 lb]
<b>What's in the Box</b>	Included in Package	1 - 30m Coax High Resolution Monitor VGA Cable - HD15 M/M  2 - Nuts

Product appearance and specifications are subject to change without notice.