

Datasheet

RS Pro Insulated Crimp Spade Connector, 1.5mm² to 2.5mm², 16AWG to 14AWG, M4 Stud Size, Blue Vinyl

RS Stock No: 149-619



Product Details

RS Pro insulated crimp spade connector in blue vinyl colour, has 1.5 mm² to 2.5 mm², 16 to 14 AWG wire size and M4 stud size. This connector has a PVC funnel entry range of crimps on reels. It is available in a variety of the most popular sizes.

Features and Benefits

- PVC funnel entry range of crimps on reels
- Available in a variety of the most popular sizes
- Red 0.5 to 1.5 mm², blue 1.5 to 2.5 mm² and yellow 4 to 6 mm²

Specifications:

Colour	Blue
Contact Material	Copper
Contact Plating	Tin
Insulation	Insulated
Insulation Material	Vinyl
Maximum Wire Size (AWG)	14 AWG
Maximum Wire Size (mm ²)	2.5 mm ²
Minimum Wire Size (AWG)	16 AWG
Minimum Wire Size (mm ²)	1.5 mm ²
Overall Length	20.1 mm
Stud Size	M4.3
Thickness	0.8 mm
Width	7.2 mm
Wire Size	16 to 14 AWG
Current Rating	27 A
Temperature Rating	+75°C
Type	Flared Vinyl without Copper Sleeve
Voltage Rating	600 V