



ENGLISH

Datasheet

Stock No: 221-046

RS Pro 1.2V NiMH Tagged Terminal 2/3 A NiMH Rechargeable Battery, 1200mAh



RS Pro, Continuous Charge Tagged

For continuous charge applications

Voltage 1.2V

Note

All batteries are supplied with only a residual charge and should be charged at the continuous charge rate before use.

Caution

Do not connect batteries in parallel

NiMH Rechargeable Industrial Batteries

Improved performance over NiCd batteries.



ENGLISH

Specifications

| | |
|-------------------------------|---------------|
| Size | 2/3 A |
| Nominal Voltage | 1.2V |
| Capacity | 1200mAh |
| Chemistry | NiMH |
| Dimensions | 28.5 x 16.8mm |
| Terminal Type | Tagged |
| Maximum Continuous Current | 3mA |
| Operating Temperature Range | -10 → +60°C |
| Minimum Operating Temperature | -10°C |
| Maximum Operating Temperature | +60°C |